



DIABLO / SMAC Antibody

CATALOG NUMBER: 70-589

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	DIABLO / SMAC Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 5 ug/mL, and Western Blotting starting at 0.5 - 2 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	A synthetic peptide corresponding to amino acids 226 to 239 of human Smac (Genbank accession no. AAF87716) .
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.2% gelatin, 0.05% sodium azide.
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DIABLO, DFNA64, DIABLO-S, Diablo homolog, mitochondrial, SMAC3, Mitochondrial Smac protein, SMAC
ACCESSION NO.:	Q9NR28
PROTEIN GI NO.:	18203316
OFFICIAL SYMBOL:	DIABLO
GENE ID:	56616

Background

FOR RESEARCH USE ONLY

December 13, 2016