



MRE11A / MRE11 Antibody

CATALOG NUMBER: 70-602

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	MRE11A / MRE11 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL, and Western Blotting starting at 1 - 2 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	A synthetic peptide of human MRE11.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.02 % sodium azide.
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MRE11A, AT-like disease, Endo/exonuclease Mre11, HNGS1, MRE11, MRE11 homolog 1, MRE11 homolog A, MRE11B, ATLD
ACCESSION NO.:	P49959
PROTEIN GI NO.:	17380137
OFFICIAL SYMBOL:	MRE11A
GENE ID:	4361

Background

FOR RESEARCH USE ONLY

December 13, 2016