




## NFYA Antibody

CATALOG NUMBER: 48-636



Immunohistochemistry staining of NFYA in prostate tissue using NFYA Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	IF, IHC, IP, WB
<b>APPLICATIONS:</b>	NFYA antibody can be used in immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	NFYA antibody was raised against a peptide corresponding to a region near the N-Terminus of NFYA (Human).
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Sterile Filtration
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Serum - liquid, 0.01% sodium azide.
<b>STORAGE CONDITIONS:</b>	Store NFYA antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	NFYA, CBF-A, CBF-B, HAP2, HAP2 CCAAT-binding protein, NF-YA
<b>ACCESSION NO.:</b>	P23511
<b>PROTEIN GI NO.:</b>	115844
<b>OFFICIAL SYMBOL:</b>	NFYA
<b>GENE ID:</b>	4800

### Background

FOR RESEARCH USE ONLY