




NFKBIA Antibody

CATALOG NUMBER: 48-730



Immunohistochemistry staining of NFKBIA
in skeletal muscle tissue using NFKBIA
Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	NFKBIA antibody can be used in ELISA, Western Blot, immunohistochemistry starting at 10 ug/mL, and immunofluorescence starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	pSer32
IMMUNOGEN:	NFKBIA antibody was raised against amino acids surrounding Ser 32 of NFKBIA (Human).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.02% sodium azide, 50% glycerol.
STORAGE CONDITIONS:	NFKBIA antibody should be stored long term (months) at -80 °C and short term (days) at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NFKBIA, IκB-α, IKBA, IkappaBalpha, MAD3, NF-kappa-B inhibitor alpha, NFKBI, I-kappa-B-alpha, IKB Alpha, MAD-3
ACCESSION NO.:	P25963
PROTEIN GI NO.:	126682
OFFICIAL SYMBOL:	NFKBIA
GENE ID:	4792

