

## SAFETY DATA SHEET

Revision Date 26-May-2017

Revision Number 2

### 1. Identification

**Product Name** 4-Methoxy-7-methyl-5H-furo[3,2-g][1]benzopyran-5-one

**Cat No. :** AC235030000; AC235030050; AC235030250

**Synonyms** Visnagin

**Recommended Use** Laboratory chemicals.

**Uses advised against** Not for food, drug, pesticide or biocidal product use

#### Details of the supplier of the safety data sheet

##### Company

Fisher Scientific  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100

Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410

##### **Emergency Telephone Number**

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11

Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99

**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

### 2. Hazard(s) identification

#### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute oral toxicity

Category 4

#### Label Elements

##### **Signal Word**

Warning

##### **Hazard Statements**

Harmful if swallowed



##### **Precautionary Statements**

###### **Prevention**

Wash face, hands and any exposed skin thoroughly after handling

Do not eat, drink or smoke when using this product

###### **Ingestion**

IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell

Rinse mouth

**Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

None identified

### 3. Composition / information on ingredients

Component	CAS-No	Weight %
4-Methoxy-7-methylfuro[3,2-g]chromen-5-one	82-57-5	97

### 4. First-aid measures

<b>Eye Contact</b>	Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
<b>Skin Contact</b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Obtain medical attention. Take off contaminated clothing and shoes immediately.
<b>Inhalation</b>	Remove from exposure, lie down. Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Immediate medical attention is required.
<b>Ingestion</b>	Never give anything by mouth to an unconscious person. Drink plenty of water. Call a physician immediately. If possible drink milk afterwards.
<b>Most important symptoms/effects Notes to Physician</b>	No information available. Treat symptomatically

### 5. Fire-fighting measures

<b>Suitable Extinguishing Media</b>	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
<b>Unsuitable Extinguishing Media</b>	No information available
<b>Flash Point</b>	No information available
<b>Method -</b>	No information available
<b>Autoignition Temperature</b>	No information available
<b>Explosion Limits</b>	
<b>Upper</b>	No data available
<b>Lower</b>	No data available
<b>Sensitivity to Mechanical Impact</b>	No information available
<b>Sensitivity to Static Discharge</b>	No information available

**Specific Hazards Arising from the Chemical**

Keep product and empty container away from heat and sources of ignition.

**Hazardous Combustion Products**

Thermal decomposition can lead to release of irritating gases and vapors

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**NFPA**

Health  
2Flammability  
0Instability  
0Physical hazards  
N/A

## 6. Accidental release measures

### Personal Precautions Environmental Precautions

Ensure adequate ventilation. Use personal protective equipment.  
See Section 12 for additional ecological information.

**Methods for Containment and Clean Up** Sweep up or vacuum up spillage and collect in suitable container for disposal.

## 7. Handling and storage

### Handling

Avoid contact with skin and eyes. Avoid contact with clothing. Remove and wash contaminated clothing before re-use. Avoid breathing vapors or mists. Do not ingest. Wash thoroughly after handling.

### Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

## 8. Exposure controls / personal protection

### Exposure Guidelines

This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

### Engineering Measures

Ventilation systems.

### Personal Protective Equipment

#### Eye/face Protection

Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

#### Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure.

#### Respiratory Protection

Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

#### Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

## 9. Physical and chemical properties

### Physical State

Powder Solid

### Appearance

Beige

### Odor

No information available

### Odor Threshold

No information available

### pH

No information available

### Melting Point/Range

139 - 142 °C / 282.2 - 287.6 °F

### Boiling Point/Range

No information available

### Flash Point

No information available

### Evaporation Rate

No information available

### Flammability (solid,gas)

No information available

### Flammability or explosive limits

#### Upper

No data available

#### Lower

No data available

### Vapor Pressure

No information available

### Vapor Density

No information available

### Specific Gravity

No information available

Solubility	No information available
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	No information available
Decomposition Temperature	No information available
Viscosity	No information available
Molecular Formula	C13 H10 O4
Molecular Weight	230.22

## 10. Stability and reactivity

Reactive Hazard	None known, based on information available
Stability	Stable under normal conditions.
Conditions to Avoid	Incompatible products.
Incompatible Materials	Oxidizing agents
Hazardous Decomposition Products	Thermal decomposition can lead to release of irritating gases and vapors
Hazardous Polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.

## 11. Toxicological information

### Acute Toxicity

Product Information No acute toxicity information is available for this product

### Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
4-Methoxy-7-methylfuro[3,2-g]chromen-5-one	LD50 = 832 mg/kg ( Rat )	Not listed	Not listed

Toxicologically Synergistic Products No information available

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation	No information available
Sensitization	No information available
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
4-Methoxy-7-methylfuro[3,2-g]chromen-5-one	82-57-5	Not listed	Not listed	Not listed	Not listed	Not listed

Mutagenic Effects No information available

Reproductive Effects No information available.

Developmental Effects No information available.

Teratogenicity No information available.

STOT - single exposure None known

STOT - repeated exposure None known

Aspiration hazard No information available

Symptoms / effects, both acute and No information available

delayed

**Endocrine Disruptor Information** No information available

**Other Adverse Effects** The toxicological properties have not been fully investigated.

## 12. Ecological information

### Ecotoxicity

Do not empty into drains.

**Persistence and Degradability** No information available

**Bioaccumulation/ Accumulation** No information available.

**Mobility** No information available.

## 13. Disposal considerations

**Waste Disposal Methods** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

## 14. Transport information

**DOT** Not regulated  
**TDG** Not regulated  
**IATA** Not regulated  
**IMDG/IMO** Not regulated

## 15. Regulatory information

### International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
4-Methoxy-7-methylfuro[3,2-g] chromen-5-one	-	-	-	201-430-3	-		-	-	-	-	-

#### Legend:

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

### U.S. Federal Regulations

**TSCA 12(b)** Not applicable

**SARA 313** Not applicable

### **SARA 311/312 Hazard Categories**

Acute Health Hazard No  
 Chronic Health Hazard No

Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA Occupational Safety and Health Administration  
Not applicable

CERCLA  
Not applicable

California Proposition 65 This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations Not applicable

#### U.S. Department of Transportation

Reportable Quantity (RQ):	N
DOT Marine Pollutant	N
DOT Severe Marine Pollutant	N

U.S. Department of Homeland Security  
This product does not contain any DHS chemicals.

#### Other International Regulations

Mexico - Grade No information available

### 16. Other information

Prepared By Regulatory Affairs  
Thermo Fisher Scientific  
Email: EMSDS.RA@thermofisher.com

Revision Date 26-May-2017

Print Date 26-May-2017

Revision Summary This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

#### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**