




ACPP Antibody [M01010921]

CATALOG NUMBER: 49-013



Human prostate tissue stained with ACPP
Antibody at 5 ug/mL followed by
biotinylated anti-mouse IgG secondary
antibody, alkaline phosphatase-streptavidin
and chromogen.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	ACPP antibody can be used in Western Blot, and immunohistochemistry starting at 20 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	PAP 100%
IMMUNOGEN:	Highly pure human PAP
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.5 with 0.1% NaN ₃
STORAGE CONDITIONS:	Store ACPP antibody at 4 °C.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ACPP, ACP3, 5-NT, 5-nucleotidase, Acid phosphatase, prostate, ACP-3, Ecto-5-nucleotidase, PAP, Prostatic acid phosphatase, Thiamine monophosphatase, Prostatic acid phosphatase, TMPase
ACCESSION NO.:	P15309
PROTEIN GI NO.:	130730
OFFICIAL SYMBOL:	ACPP
GENE ID:	55

