




HGF Antibody [7-2]

CATALOG NUMBER: 49-034



Human cerebellum, white matter tissue
stained with HGF Antibody at 10 ug/mL
followed by biotinylated anti-mouse IgG
secondary antibody, alkaline phosphatase-
streptavidin and chromogen.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	HGF antibody can be used in ELISA, Western Blot, immunohistochemistry starting at 5 ug/mL, and immunofluorescence starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Reacts with human HGF and to a lesser extent, mouse by Western Blot.
IMMUNOGEN:	Human HGF
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.01% sodium azide
STORAGE CONDITIONS:	Store HGF antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HGF, DFNB39, Hepatocyte growth factor, Hepatopoietin-A, Hepapoiectin A, Hepatopoiectin-A, Scatter factor), SF, F-TCF, HGFB, HPTA, Scatter factor
ACCESSION NO.:	P14210
PROTEIN GI NO.:	123116
OFFICIAL SYMBOL:	HGF

Background

FOR RESEARCH USE ONLY

December 13, 2016