




## CBR3 Antibody [AT3C5]

CATALOG NUMBER: 49-078



Human brain cortex, White Matter tissue  
stained with Antibody, alkaline  
phosphatase-streptavidin and chromogen.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, IHC, WB
<b>APPLICATIONS:</b>	CBR3 antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Recombinant CBR3 (1-277aa) purified from E. coli
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein G Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, pH 7.4, 0.1% sodium azide
<b>STORAGE CONDITIONS:</b>	Aliquot and store CBR3 antibody at -20 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	CBR3, Carbonyl reductase [NADPH] 3, Carbonyl reductase (NADPH) 3, Carbonyl reductase 3, HCBR3, SDR21C2
<b>ACCESSION NO.:</b>	O75828
<b>PROTEIN GI NO.:</b>	6014959
<b>OFFICIAL SYMBOL:</b>	CBR3
<b>GENE ID:</b>	874

### Background

