




## CD74 Antibody [LN2]

CATALOG NUMBER: 49-209



Immunohistochemistry staining of CD74 in thymus tissue using CD74 monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Baboon, Human
<b>TESTED APPLICATIONS:</b>	FACS, IHC, IP
<b>APPLICATIONS:</b>	CD74 antibody can be used in ELISA starting at 1:5000 - 1:40000, Western Blot starting at 1:5000 - 1:40000, and immunohistochemistry starting at 5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	SU-DHL-4 cells
<b>IMMUNOGEN:</b>	CD74 monoclonal antibody was raised against SU - DHL - 4 cells (Human).
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Affinity Chromatography
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Phosphate-buffered solution, pH 7.2, 0.09% sodium azide.
<b>STORAGE CONDITIONS:</b>	Store CD74 antibody undiluted at 4 °C.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	CD74, CD74 antigen, DHLAG, HLADG, HLA-DR-gamma, Ia-associated invariant chain, p33, MHC HLA-DR gamma chain, Ia-GAMMA
<b>ACCESSION NO.:</b>	P04233
<b>PROTEIN GI NO.:</b>	20178292
<b>OFFICIAL SYMBOL:</b>	CD74
<b>GENE ID:</b>	972

FOR RESEARCH USE ONLY

December 13, 2016