




CD59 Antibody [MEM-43]

CATALOG NUMBER: 49-357



Immunohistochemistry staining of CD59 in skin, sweat glands formlin-fixed paraffin-embedded tissue using CD59 monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, FACS, IHC, IP, WB
APPLICATIONS:	CD59 antibody can be used in ELISA, and immunohistochemistry starting at 10 ug/mL. This product requires antigen retrieval using heat treatment methods prior to staining of paraffin sections. Sodium citrate buffer pH 6.0 is recommended for this purpose. IHC Control: Tonsil.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	IgG Fractionation
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.09% sodium azide.
STORAGE CONDITIONS:	Store CD59 antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CD59, 16.3A5, 1F5, 1F5 antigen, CD59 glycoprotein, EL32, EJ16, G344, HRF-20, MAC-IP, MACIF, Ly-6-like protein, MEM43, M1RL, MEM43 antigen, MIN2, MIN3, MSK21, p18-20, Protectin, MAC-inhibitory protein, MIC11, T cell-activating protein, CD59 antigen, EJ30, HRF20, Human leukocyte antigen MIC11, Lymphocytic antigen CD59/MEM43, MIN1
ACCESSION NO.:	P13987
PROTEIN GI NO.:	116021
OFFICIAL SYMBOL:	CD59
GENE ID:	966

