




## ICOS Antibody

CATALOG NUMBER: 49-679



Immunohistochemistry staining of ICOS in spleen tissue using ICOS Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, IHC
<b>APPLICATIONS:</b>	ICOS antibody can be used in ELISA starting at 1:20000 - 1:100000, Western Blot starting at 1:2000 - 1:10000, and immunohistochemistry starting at 1:500.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Amino acids 171 to 186 of human ICOS
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Protein G Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS with 0.09% Sodium Azide
<b>STORAGE CONDITIONS:</b>	ICOS antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	ICOS, ALIM, CD278, CVID1, Inducible costimulator, Inducible T-cell co-stimulator, CD278 antigen, Inducible T-cell costimulator
<b>ACCESSION NO.:</b>	Q9Y6W8
<b>PROTEIN GI NO.:</b>	50400701
<b>OFFICIAL SYMBOL:</b>	ICOS
<b>GENE ID:</b>	29851

### Background

FOR RESEARCH USE ONLY

