



VIM Antibody [23H2]

CATALOG NUMBER: 70-073

Specifications

SPECIES REACTIVITY:	Human, Rat
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	VIM Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:400 and Western Blot starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human protein purified from E. coli (His-Vimentin).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	VIM Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. Store undiluted.
CLONALITY:	Monoclonal
ISOTYPE:	IgG3,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	VIM, Vimentin
ACCESSION NO.:	P08670
PROTEIN GI NO.:	55977767
OFFICIAL SYMBOL:	VIM
GENE ID:	7431

Background

FOR RESEARCH USE ONLY

December 13, 2016