



RRAS Antibody [6A8]

CATALOG NUMBER: 70-075

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	RRAS Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 1:400 and Western Blot starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human protein purified from E. coli (His-R-Ras).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	RRAS Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. Store undiluted.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RRAS, Oncogene RRAS, R-ras, Ras-related protein R-Ras2, p23, Ras-related protein R-Ras
ACCESSION NO.:	P10301
PROTEIN GI NO.:	133486
OFFICIAL SYMBOL:	RRAS
GENE ID:	6237

Background

FOR RESEARCH USE ONLY

December 13, 2016