



PDIA3 Antibody [Map.ERP57]

CATALOG NUMBER: 70-328

Specifications

SPECIES REACTIVITY:	Bovine, Dog, Guinea Pig, Hamster, Human, Monkey, Mouse, Pig, Rabbit, Rat
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	PDIA3 antibody can be used for staining paraffin embeded tissues starting at 15 ug/mL, and Western Blot starting at 1:20000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Detects ~57 kD protein.
IMMUNOGEN:	Human Recombinant Erp57 (Grp58).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PDIA3, 58 kDa microsomal protein, ER protein 57, ERp60, ERp61, Disulfide isomerase ER-60, Endoplasmic reticulum P58, GRP58, HsT17083, p58, Phospholipase C-alpha, PI-PLC, ER protein 60, ER60, ERp57, GRP57, Protein disulfide-isomerase A3
ACCESSION NO.:	P30101
PROTEIN GI NO.:	2507461
OFFICIAL SYMBOL:	PDIA3
GENE ID:	2923

Background

FOR RESEARCH USE ONLY

December 13, 2016