



DAXX Antibody

CATALOG NUMBER: 70-452

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:66), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	DAXX Antibody detects endogenous levels of total DAXX protein.
IMMUNOGEN:	Synthetic peptide from human Daxx.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DAXX, BING2, CENP-C binding protein, DAP6, Death-associated protein 6, EAP1, Fas-binding protein, HDaxx, ETS1-associated protein 1
ACCESSION NO.:	Q9UER7
PROTEIN GI NO.:	24636785
OFFICIAL SYMBOL:	DAXX
GENE ID:	1616

Background

FOR RESEARCH USE ONLY

December 13, 2016