



ANXA2 / Annexin A2 Antibody

CATALOG NUMBER: 70-494

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ANXA2 / Annexin A2 Antibody can be used for ELISA starting at 1:1000, and Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	KLH-conjugated synthetic peptide between amino acids 19-49 from N-terminal region of human ANXA2.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
BUFFER:	PBS, 0.09% sodium azide
CONCENTRATION:	0.25 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ANXA2, Annexin A2, Annexin-2, ANX2, Calpactin I heavy chain, Chromobindin-8, CAL1H, Calpactin I heavy polypeptide, Chromobindin 8, LPC2, LIP2, Lipocortin II, p36, LPC2D, PAP-IV, Protein I, Annexin II, ANX2L4, Calpactin-1 heavy chain
ACCESSION NO.:	P07355
PROTEIN GI NO.:	113950
OFFICIAL SYMBOL:	ANXA2
GENE ID:	302

Background

FOR RESEARCH USE ONLY

December 13, 2016