



ALDOA / Aldolase Antibody

CATALOG NUMBER: 70-497

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: IHC, WB

APPLICATIONS: ALDOA / Aldolase Antibody can be used for ELISA starting at 1:1000, and Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL,

USER NOTE: Optimal dilutions for each application to be determined by the researcher.

IMMUNOGEN: KLH-conjugated synthetic peptide between amino acids 66-95 from N-terminal region of human Aldolase (ALDOA).

HOST SPECIES: Rabbit

Properties

PURIFICATION: Ammonium Sulfate Precipitation

BUFFER: PBS, 0.09% sodium azide

CONCENTRATION: 0.25 mg/ml

STORAGE CONDITIONS: Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: ALDOA, ALDA, Aldolase, GSD12, Muscle-type aldolase, Lung cancer antigen NY-LU-1

ACCESSION NO.: P04075

PROTEIN GI NO.: 113606

OFFICIAL SYMBOL: ALDOA

GENE ID: 226

Background

FOR RESEARCH USE ONLY

December 13, 2016