



CDH13 / H Cadherin Antibody

CATALOG NUMBER: 70-503

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, FACS, IHC, WB
APPLICATIONS:	CDH13 / H Cadherin Antibody can be used for ELISA starting at 1:1000, Flow Cytometry starting at 1:10 - 1:50, Immunohistochemistry in paraffin embeded tissues starting at 10ug/mL, and Western Blotting starting at 1:50 - 1:100.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	KLH-conjugated synthetic peptide between amino acids 589-617 from C-terminal region of human H Cadherin (CDH13).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein A Column
BUFFER:	PBS, 0.09% sodium azide
CONCENTRATION:	0.25 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CDH13, Cadherin-13, CDHH, Cdht, Heart cadherin, H-cadherin, T-cad, T-cadherin, Truncated cadherin, p105
ACCESSION NO.:	P55290
PROTEIN GI NO.:	1705552
OFFICIAL SYMBOL:	CDH13
GENE ID:	1012

Background

FOR RESEARCH USE ONLY

December 13, 2016