



C20orf141 Antibody

CATALOG NUMBER: 30-829



Antibody used in WB on Human Jurkat
0.2-1 ug/ml.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	C20orf141 antibody can be used for detection of C20orf141 by ELISA at 1:62500. C20orf141 antibody can be used for detection of C20orf141 by western blot at 1 ug/mL, and HRP conjugated secondary antibody should be diluted 1:50,000 - 100,000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. 1219 - MCF7 Cell Lysate
PREDICTED MOLECULAR WEIGHT:	17 kDa
IMMUNOGEN:	Antibody produced in rabbits immunized with a synthetic peptide corresponding a region of human C20orf141.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Antibody is purified by peptide affinity chromatography method.
PHYSICAL STATE:	Lyophilized
BUFFER:	Antibody is lyophilized in PBS buffer with 2% sucrose. Add 50 uL of distilled water. Final antibody concentration is 1 mg/mL.
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	For short periods of storage (days) store at 4°C. For longer periods of storage, store C20orf141 antibody at -20°C. As with any antibody avoid repeat freeze-thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	C20orf141, MGC26144, dJ860F19.4
ACCESSION NO.:	NP_542777
PROTEIN GI NO.:	18152771

OFFICIAL SYMBOL: C20orf141

GENE ID: 128653

Background

BACKGROUND: C20orf141 is a single-pass membrane protein. The exact function of C20orf141 remains unknown.

REFERENCES: 1) Deloukas, P., (2001) Nature 414 (6866), 865-871.

FOR RESEARCH USE ONLY

December 12, 2016