




TRIP Antibody

CATALOG NUMBER: 46-529



Western blot analysis of TRIP in human testis lysate (RIPA buffer, 30 ug total protein per lane) using TRIP Antibody at 1 ug/mL.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:2000. Approximately 50 kDa band observed in human testis lysates (calculated MW of 53.3 kDa according to NP_005870.2). Recommended concentration: 2.0 ug/mL. An additional band of unknown identity was also consistently observed at 38 kDa. This band was successfully blocked by incubation with the immunizing peptide.
POSITIVE CONTROL:	1) Cat. No. 1313 - Human Testis Tissue Lysate
IMMUNOGEN:	TRIP antibody was raised against a 13 amino acid synthetic peptide near the C-Terminus of TRIP.
HOST SPECIES:	Goat

Properties

PURIFICATION:	TRIP antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	TRIP antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TRAIP, TRAF interacting protein, TRIP, RNF206, ring finger protein 206
ACCESSION NO.:	NP_005870
PROTEIN GI NO.:	40807469
OFFICIAL SYMBOL:	TRAIP

GENE ID: 10293

Background

REFERENCES: 1) Lee SY, Lee SY, Choi Y. TRAF-interacting protein (TRIP): a novel component of the tumor necrosis factor receptor (TNFR)- and CD30-TRAF signaling complexes that inhibits TRAF2-mediated NF-kappaB activation. J Exp Med. 1997 Apr 7;185(7):1275-85.

FOR RESEARCH USE ONLY

December 13, 2016