



## Forkhead Box I2 Antibody

CATALOG NUMBER: 46-843

### Specifications

#### SPECIES REACTIVITY:

**TESTED APPLICATIONS:** ELISA

**APPLICATIONS:** ELISA: Antibody detection limit dilution 1:8,000.

**IMMUNOGEN:** Forkhead Box I2 antibody was raised against an 11 amino acid synthetic peptide near the C-Terminus of Forkhead Box I2.

**HOST SPECIES:** Goat

### Properties

**PURIFICATION:** Forkhead Box I2 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

**PHYSICAL STATE:** Liquid

**BUFFER:** Forkhead Box I2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

**CONCENTRATION:** 500 ug/mL

**STORAGE CONDITIONS:** Aliquot and store at -20°C. Minimize freezing and thawing.

**CLONALITY:** Polyclonal

**CONJUGATE:** Unconjugated

### Additional Info

**ALTERNATE NAMES:** Foxi2 [Mus musculus], forkhead box I2, MGI:3028075, B130055A05Rik , B130055A05Rik

**ACCESSION NO.:** NP\_899016.1

**PROTEIN GI NO.:** 34147250

**OFFICIAL SYMBOL:** Foxi2

**GENE ID:** 270004 (mouse); 246073 (rat);

### Background

**REFERENCES:** 1) Ohyama T, Groves AK. Expression of mouse Foxi class genes in early craniofacial development. Dev Dyn. 2004 Nov;231(3):640-6.

**FOR RESEARCH USE ONLY**

December 13, 2016