



## RNF212 Antibody

CATALOG NUMBER: 46-893

### Specifications

#### SPECIES REACTIVITY:

**TESTED APPLICATIONS:** ELISA

**APPLICATIONS:** ELISA: Antibody detection limit dilution 1:16,000.

**IMMUNOGEN:** RNF212 antibody was raised against a 13 amino acid synthetic peptide near the internal region of RNF212.

**HOST SPECIES:** Goat

### Properties

**PURIFICATION:** RNF212 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

**PHYSICAL STATE:** Liquid

**BUFFER:** RNF212 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

**CONCENTRATION:** 500 ug/mL

**STORAGE CONDITIONS:** Aliquot and store at -20°C. Minimize freezing and thawing.

**CLONALITY:** Polyclonal

**CONJUGATE:** Unconjugated

### Additional Info

**ALTERNATE NAMES:** RNF212, ring finger protein 212, FLJ38841, MGC120227, MGC120228, -, ZHP3

**ACCESSION NO.:** NP\_919420.1

**PROTEIN GI NO.:** 37059810

**OFFICIAL SYMBOL:** RNF212

**GENE ID:** 285498

### Background

**REFERENCES:** 1) Kong A, Thorleifsson G, Stefansson H, Masson G, Helgason A, Gudbjartsson DF, Jonsdottir GM, Gudjonsson SA, Sverrisson S, Thorlacius T, Jonasdottir A, Hardarson GA, Palsson ST, Frigge ML, Gulcher JR, Thorsteinsdottir U, Stefansson K Sequence Variants in the RNF212 Gene Associate with Genomewide Recombination Rate Science. 2008 Jan 31

FOR RESEARCH USE ONLY

December 13, 2016