



Dao Antibody

CATALOG NUMBER: 42-926

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:1000. Western Blot: Preliminary experiments in Mouse and Rat Brain, Fetal Brain, Kidney and Liver lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any

IMMUNOGEN: Dao Antibody was raised against a 15 amino acid sequence near the internal region of Dao (mouse).

HOST SPECIES: Goat

Properties

PURIFICATION: Antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: Dao antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: Dao, OTTMUSP00000028675, OTTMUSP00000028673, Dao-1, Dao1, DAMOX, D-amino-acid oxidase, D-amino acid oxidase 1, DAAO, A1987963

ACCESSION NO.: NP_034148.2

PROTEIN GI NO.: 110815857

OFFICIAL SYMBOL: Dao

GENE ID: 13142 (mouse); 114027 (rat);

Background

FOR RESEARCH USE ONLY

December 13, 2016