



DNAH8 Antibody

CATALOG NUMBER: 42-641

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:128000. Western Blot: Not yet tested - our routinely used western blotting protocol does not allow detection of proteins as large as the calculated size of 515kDa according to NP_001362.2. Therefore we cannot recommend an optimal concentration and the antibody i

IMMUNOGEN: DNAH8 antibody was raised against a 12 amino acid synthetic peptide near the internal region of DNAH8 (aa 1738-1749).

HOST SPECIES: Goat

Properties

PURIFICATION: DNAH8 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: DNAH8 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: DNAH8, hdhc9, FLJ36334, FLJ36115, FLJ25850, dynein, axonemal, heavy polypeptide 8, heavy chain 8, ATPase

ACCESSION NO.: NP_001362.2

PROTEIN GI NO.: 126012497

OFFICIAL SYMBOL: DNAH8

GENE ID: 1769

Background

FOR RESEARCH USE ONLY

December 13, 2016