



TFAP2D Antibody

CATALOG NUMBER: 42-283

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:2000. Western Blot: Preliminary experiments in human Ileum and skeletal muscle lysates gave no specific signal but low background (at antibody concentration up to 1 ug/mL).

IMMUNOGEN: TFAP2D antibody was raised against a 13 amino acid synthetic peptide near the internal region of TFAP2D.

HOST SPECIES: Goat

Properties

PURIFICATION: TFAP2D antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: TFAP2D antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: TFAP2D, transcription factor AP-2 beta-like 1, transcription factor AP-2 beta (activating enhancer-binding protein 2 beta)-like 1, transcription factor AP-2 beta (activating enhancer binding protein 2 beta)-like 1, activating enhancer binding protein 2 beta-like 1, OTTHUMP00000016593, AP-2 like, TFAP2BL1, transcription factor AP-2 delta (activating enhancer binding protein 2 delta), TFAP2D

ACCESSION NO.: NP_758438.2

PROTEIN GI NO.: 151301211

OFFICIAL SYMBOL: TFAP2D

GENE ID: 83741

Background

REFERENCES: 1) Wenke AK, Rothhammer T, Moser M, Bosserhoff AK Regulation of integrin alpha10 expression in chondrocytes by the transcription factors AP-2epsilon and Ets-1 Biochem Biophys Res Commun. 2006 Jun 23;345(1):495-501. Epub 2006 May 2

FOR RESEARCH USE ONLY

December 13, 2016