



Safety Data Sheet

SECTION 1: Identification

1.1. Product Identifier

Trade Name or Designation: VeriSpec™ Antimony Standard for ICP/MS 100 ppm in 2% HNO₃/HF
Manufactured and Tested in an ISO 17025/Guide 34 Accredited Facility

Product Number: RV010550

Other Identifying Product Numbers: RV010550-100N

1.2. Recommended Use and Restrictions on Use

Calibration Standard

1.3. Details of the Supplier of the Safety Data Sheet

Company: Ricca Chemical Company

Address: 448 West Fork Drive
Arlington, TX 76012 USA

Telephone: 888-467-4222

1.4. Emergency Telephone Number (24 hr)

CHEMTREC (USA) 800-424-9300
CHEMTREC (International) 1+ 703-527-3887

SECTION 2: Hazard(s) Identification

2.1. Classification of the Substance or Mixture (in accordance with OSHA HCS 29 CFR 1910.1200)

For the full text of the Hazard and Precautionary Statements listed below, see Section 16.

Hazard Class	Category	Hazard	
		Statement	Precautionary Statements
Skin Corrosion / Irritation	Category 2	H315	P264, P280, P302+P352, P321, P332+P313, P362
Eye Damage / Irritation	Category 2A	H319	P264, P280, P305+P351+P338, P337+P313

2.2. GHS Label Elements

Pictograms:



Signal Word: **Warning**

Safety Data Sheet

Hazard Statements:

Hazard Number	Hazard Statement
H315	Causes skin irritation.
H319	Causes serious eye irritation.

Precautionary Statements:

Precautionary Number	Precautionary Statement
P264	Wash arms, hands and face thoroughly after handling.
P280	Wear protective gloves and eye protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P321	Specific treatment (Wash areas of contact with water immediately).
P332+P313	If skin irritation occurs: Get medical attention.
P337+P313	If eye irritation persists: Get medical attention.
P362	Take off contaminated clothing and wash it before reuse.

2.3. WHMIS Classification

WHMIS classification is not included based on the recommended option (Option 4) found in the Canada Gazette Part II, Vol. 149, No.3, page 458

2.4. Hazards not Otherwise Classified or Covered by GHS

Data not available.

SECTION 3: Composition / Information on Ingredients

3.1. Components of Substance or Mixture

Chemical Name	Formula	Molecular Weight	CAS Number	Weight%
Water	H ₂ O	18.01 g/mol	7732-18-5	97.48%
Nitric Acid	HNO ₃	63.01 g/mol	7697-37-2	2.00%
Hydrofluoric Acid	HF	20.00 g/mol	7664-39-3	0.50%
Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)-	F ₆ Sb-H	Data not available.	16950-06-4	0.02%

SECTION 4: First-Aid Measures

4.1. General First Aid Information

Eye Contact: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Inhalation: Not expected to require first aid. If necessary, remove to fresh air.



Safety Data Sheet

Skin Contact: IF ON SKIN: Wash with plenty of soap and water.

Ingestion: No action required to be taken. If necessary, dilute with water.

4.2. Most Important Symptoms and Effects, Acute and Delayed

May cause mild irritation to areas of contact.

4.3. Medical Attention or Special Treatment Needed

Specific treatment (Wash areas of contact with water immediately).

SECTION 5: Fire-Fighting Measures

5.1. Extinguishing Media

Not considered to be a fire or explosion hazard.

5.2. Specific Hazards Arising from the Substance or Mixture

Not considered to be a fire or explosion hazard.

5.3. Special Protective Equipment for Firefighters

Wear protective clothing and NIOSH-approved breathing equipment appropriate for the surrounding fire.

SECTION 6: Accidental Release Measures

6.1. Personal Precautions, Protective Equipment and Emergency Procedures

Wear protective gloves and eye protection.

6.2. Cleanup and Containment Methods and Materials

Absorb with suitable material and dispose of in accordance with local regulations.

SECTION 7: Handling and Storage

7.1. Precautions for Safe Handling and Storage Conditions

Protect from freezing and physical damage.



Safety Data Sheet

SECTION 8: Exposure Controls / Personal Protection

8.1. Control Parameters

Chemical Name	Limit Type	Country	Exposure Limit	Information Source
Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (16950-06-4)	TWA	USA	0.5 mg/m ³ TWA (as Sb)	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (16950-06-4)	TLV-TWA	USA	0.5 mg/m ³ TWA (as Sb)	ACGIH - Threshold Limit Values - Time Weighted Averages (TLV-TWA)
Hydrofluoric Acid (7664-39-3)	TWA	USA	3 ppm TWA (as F)	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Hydrofluoric Acid (7664-39-3)	TWA	USA	2.5 mg/m ³ TWA (as F) 2.5 mg/m ³ TWA (dust)	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Hydrofluoric Acid (7664-39-3)	TLV-Ceiling	USA	2 ppm Ceiling (as F)	ACGIH - Threshold Limit Values - Ceilings (TLV-C)
Hydrofluoric Acid (7664-39-3)	TLV-TWA	USA	2.5 mg/m ³ TWA (as F)	ACGIH - Threshold Limit Values - Time Weighted Averages (TLV-TWA)
Hydrofluoric Acid (7664-39-3)	TLV-TWA	USA	0.5 ppm TWA (as F)	ACGIH - Threshold Limit Values - Time Weighted Averages (TLV-TWA)
Nitric Acid (7697-37-2)	TWA	USA	2 ppm TWA 5 mg/m ³ TWA	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Nitric Acid (7697-37-2)	TLV-STEEL	USA	4 ppm STEEL	ACGIH - Threshold Limit Values - Short Term Exposure Limits (TLV-STEEL)
Nitric Acid (7697-37-2)	TLV-TWA	USA	2 ppm TWA	ACGIH - Threshold Limit Values - Time Weighted Averages (TLV-TWA)

8.2. Exposure Controls

Engineering Controls: No specific controls are needed. Normal room ventilation is adequate.

Respiratory Protection: No specific controls are needed. Normal room ventilation is adequate

Skin Protection: Wear protective gloves and eye protection.

Eye Protection: Wear protective gloves and eye protection.

8.3. Personal Protective Equipment

Wear protective gloves and eye protection.



Safety Data Sheet

SECTION 9: Physical and Chemical Properties

9.1. Basic Physical and Chemical Properties

Appearance: Data not available.

Physical State: Liquid

Odor: Data not available.

Odor Threshold: Data not available.

pH: Data not available.

Melting/Freezing Point: Data not available.

Initial Boiling Point /Range: Data not available.

Flash Point: Data not available.

Evaporation Rate: Data not available.

Flammability: Data not available.

Flammability/Explosive Limits: Data not available.

Vapor Pressure: Data not available.

Vapor Density: Data not available.

Relative Density: 1.00

Solubility: Data not available.

Partition Coefficient (n-Octanol/Water): Data not available.

Auto-Ignition Temperature: Data not available.

Decomposition Temperature: Data not available.

Viscosity: Data not available.

Explosive Properties: Data not available.

Oxidizing Properties: Data not available.

SECTION 10: Stability and Reactivity

10.1. Reactivity and Chemical Stability

Stable under normal conditions of use and storage.

10.2. Possibility of Hazardous Reactions

Data not available.

10.3. Conditions to Avoid and Incompatible Materials

Protect from freezing and physical damage.

10.4. Hazardous Decomposition Products

May emit irritating fumes when heated to decomposition.



Safety Data Sheet

SECTION 11: Toxicological Information

11.1. Information on Toxicological Effects

Acute Toxicity - Oral Exposure:

Not applicable.

Acute Toxicity - Dermal Exposure:

Not applicable.

Acute Toxicity - Inhalation Exposure:

Not applicable.

Acute Toxicity - Other Information:

Data not available.

Skin Corrosion and Irritation:

Causes skin irritation. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF ON SKIN: Wash with plenty of soap and water. Specific treatment (Wash areas of contact with water immediately). If skin irritation occurs: Get medical attention. Take off contaminated clothing and wash it before reuse.

Serious Eye Damage and Irritation:

Causes serious eye irritation. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

Respiratory Sensitization:

Not applicable.

Skin Sensitization:

Not applicable.

Germ Cell Mutagenicity:

Not applicable.

Carcinogenicity:

Not applicable.

Reproductive Toxicity:

Not applicable.

Specific Target Organ Toxicity from Single Exposure:

Not applicable.

Specific Target Organ Toxicity from Repeated Exposure:

Not applicable.

Aspiration Hazard:

Not applicable.



Safety Data Sheet

Additional Toxicology Information:

Data not available.

SECTION 12: Ecological Information

12.1. Ecotoxicity

Not applicable.

12.2. Persistence and Degradability

Data not available.

12.3. Bioaccumulative Potential

Data not available.

12.4. Mobility in Soil

Data not available.

12.5. Other Adverse Ecological Effects

Data not available.

SECTION 13: Disposal Considerations

13.1. Waste Treatment Methods

Data not available.

SECTION 14: Transportation Information

14.1. Transportation by Land - Department of Transportation (DOT, United States of America)

Not regulated according to DOT Regulations.



Safety Data Sheet

Not regulated according to IATA Regulations.

SECTION 15: Regulatory Information

15.1. Occupational Safety and Health Administration (OSHA) Hazards

Not listed.

15.2. Superfund Amendments and Reauthorization Act (SARA) 302 Extremely Hazardous Substances

Hydrofluoric Acid (CAS # 7664-39-3): 100 lb EPCRA RQ

Hydrofluoric Acid (CAS # 7664-39-3): 100 lb TPQ

Nitric Acid (CAS # 7697-37-2): 1000 lb EPCRA RQ

Nitric Acid (CAS # 7697-37-2): 1000 lb TPQ

15.3. Superfund Amendments and Reauthorization Act (SARA) 311/312 Hazardous Chemicals

Hydrofluoric Acid (CAS # 7664-39-3): 100 lb final RQ; 45.4 kg final RQ

Nitric Acid (CAS # 7697-37-2): 1000 lb final RQ; 454 kg final RQ

15.4. Superfund Amendments and Reauthorization Act (SARA) 313 Toxic Release Inventory (TRI)

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): 1.0 % de minimis concentration (listed under Chemical Category N010)

Hydrofluoric Acid (CAS # 7664-39-3): 1.0 % de minimis concentration

Nitric Acid (CAS # 7697-37-2): 1.0 % de minimis concentration

15.5. Massachusetts Right-to-Know Substance List

Hydrofluoric Acid (CAS # 7664-39-3): Extraordinarily hazardous

Nitric Acid (CAS # 7697-37-2): Extraordinarily hazardous

15.6. Pennsylvania Right-to-Know Hazardous Substances

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): Environmental hazard

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): Present

Hydrofluoric Acid (CAS # 7664-39-3): Environmental hazard

Hydrofluoric Acid (CAS # 7664-39-3): Present

Nitric Acid (CAS # 7697-37-2): Environmental hazard

Nitric Acid (CAS # 7697-37-2): Present

Water (CAS # 7732-18-5): Present



Safety Data Sheet

15.7. New Jersey Worker and Community Right-to-Know Components

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): sn 2223
Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): SN 2223 500 lb TPQ (Category Code N010)
Hydrofluoric Acid (CAS # 7664-39-3): corrosive
Hydrofluoric Acid (CAS # 7664-39-3): sn 0936
Hydrofluoric Acid (CAS # 7664-39-3): sn 3759
Hydrofluoric Acid (CAS # 7664-39-3): SN 3759 100 lb TPQ; SN 1014 500 lb TPQ (Hydrogen fluoride gas only)
Nitric Acid (CAS # 7697-37-2): corrosive; reactive - second degree
Nitric Acid (CAS # 7697-37-2): sn 1356
Nitric Acid (CAS # 7697-37-2): SN 1356 500 lb TPQ
Nitric Acid (CAS # 7697-37-2): sn 3722
Nitric Acid (CAS # 7697-37-2): SN 3722 500 lb TPQ (water dissociable, Category Code N511)

15.8. California Proposition 65

Not listed.

15.9. Canada Domestic Substances List / Non-Domestic Substances List (DSL/NDSL)

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): Present (NDSL)
Hydrofluoric Acid (CAS # 7664-39-3): Present (DSL)
Nitric Acid (CAS # 7697-37-2): Present (DSL)
Water (CAS # 7732-18-5): Present (DSL)

15.10. United States of America Toxic Substances Control Act (TSCA) List

Antimonate(1-), hexafluoro-, hydrogen, (OC-6-11)- (CAS # 16950-06-4): Present
Hydrofluoric Acid (CAS # 7664-39-3): Present [T]
Nitric Acid (CAS # 7697-37-2): Present
Water (CAS # 7732-18-5): Present

15.11. European Inventory of Existing Commercial Chemical Substances (EINECS), European List of Notified Chemical Substances (ELINCS), and No Longer Polymers (NLP)

Not listed.

SECTION 16: Other Information

16.1. Full Text of Hazard Statements and Precautionary Statements

Causes skin irritation. Causes serious eye irritation.

Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection.

IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Specific treatment (Wash areas of contact with water immediately). If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing and wash it before reuse.



Safety Data Sheet

16.2. Miscellaneous Hazard Classes

Canadian Carcinogenicity Hazard Class: Not Applicable.


Physical Hazards Not Otherwise Classified (PHNOC): Not Applicable.

Health Hazards Not Otherwise Classified (HHNOC): Not Applicable.

Biohazardous Infectious Materials Hazard Class: Not Applicable.

16.3. National Fire Protection Association (NFPA) Rating

Health: 1
Flammability: 0
Reactivity: 0
Special Hazard:





Safety Data Sheet

16.4. Document Revision

Last Revision Date: 9/7/2016

DISCLAIMER

When handled properly by qualified personnel, the product described herein does not present a significant health or safety hazard. Alteration of its characteristics by concentration, evaporation, addition of other substances, or other means may present hazards not specifically addressed herein and which must be evaluated by the user. The information furnished herein is believed to be accurate and represents the best data currently available to us. No warranty, expressed or implied, is made and RICCA CHEMICAL COMPANY assumes no legal responsibility or liability whatsoever resulting from its use.