



THAP11 Antibody

CATALOG NUMBER: 42-208

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:1000. Western Blot: Approximately 26 kDa band in human Umbilical Cord lysates after 1 ug/mL antibody staining. 5 kDa according to NP_065190.2. The 26 kDa band was successfully blocked by incubation with the immunizing peptide.
IMMUNOGEN:	THAP11 antibody was raised against a 15 amino acid synthetic peptide near the internal region of THAP11.
HOST SPECIES:	Goat

Properties

PURIFICATION:	THAP11 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	THAP11 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	THAP11, THAP domain-containing protein 11, RONIN, HRIHFB2206, CTG-B45d, CTG-B43a, THAP domain containing 11, THAP11
ACCESSION NO.:	NP_065190.2
PROTEIN GI NO.:	40354197
OFFICIAL SYMBOL:	THAP11
GENE ID:	57215

Background

REFERENCES:	1) Zhu CY, Li CY, Li Y, Zhan YQ, Li YH, Xu CW, Xu WX, Sun HB, Yang XM, Cell growth suppression by thanatos-associated protein 11(THAP11) is mediated by transcriptional downregulation of c-Myc. Cell death and differentiation 2009 Mar 16 (3): 395-405.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016