



DGKQ Antibody

CATALOG NUMBER: 43-064

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:128000. Western Blot: Preliminary experiments in Human Brain lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any results been reported with other antibo

IMMUNOGEN: DGKQ antibody was raised against a 14 amino acid peptide near the internal region of DGKQ (aa295-298).

HOST SPECIES: Goat

Properties

PURIFICATION: DGKQ antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: DGKQ antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: DAG kinase theta, DAGK, DAGK4, DAGK7, DGKQ, DGK-theta, diacylglycerol kinase theta, diacylglycerol kinase, theta 110kDa, diglyceride kinase theta, OTTHUMP00000112179, OTTHUMP00000217323

ACCESSION NO.: NP_001338.2

PROTEIN GI NO.: 40806175

OFFICIAL SYMBOL: DGKQ

GENE ID: 1609

Background

FOR RESEARCH USE ONLY

December 13, 2016