




RANBP9 Antibody

CATALOG NUMBER: 46-265



Western blot analysis of RANBP9 in
paraffin embedded human tonsil using
RANBP9 Antibody at 3 ug/mL.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:16,000.
POSITIVE CONTROL:	1) Cat. No. 1315 - Human Tonsil Tissue Lysate
SPECIFICITY:	This product is also expected to recognize the centrosome-associated truncated isoform RANBPM (BAA23216.1).
IMMUNOGEN:	RANBP9 antibody was raised against a 13 amino acid synthetic peptide near the C-Terminus of RANBP9.
HOST SPECIES:	Goat

Properties

PURIFICATION:	RANBP9 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	RANBP9 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RANBP9, RAN binding protein 9, RANBPM, RanBPM, novel centrosomal protein RanBPM, ran binding protein, centrosomal
ACCESSION NO.:	NP_005484.2
PROTEIN GI NO.:	39812378
OFFICIAL SYMBOL:	RANBP9
GENE ID:	10048

Background

REFERENCES: 1) Wang D, Li Z, Messing EM, Wu G. Activation of Ras/Erk pathway by a novel MET-interacting protein RanBPM. J Biol Chem. 2002 Sep 27;277(39):36216-22. Epub 2002 Jul 29.

FOR RESEARCH USE ONLY

December 13, 2016