



SPHAR Antibody

CATALOG NUMBER: 46-427

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:2,000.

IMMUNOGEN: SPHAR antibody was raised against a 13 amino acid synthetic peptide near the C-Terminus of SPHAR.

HOST SPECIES: Goat

Properties

PURIFICATION: SPHAR antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: SpH AR antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: SPHAR, S-phase response (cyclin-related), RP4-803J11.4

ACCESSION NO.: NP_006533

PROTEIN GI NO.: 5730063

OFFICIAL SYMBOL: SPHAR

GENE ID: 10638

Background

REFERENCES: 1) Digweed M, Gunthert U, Schneider R, Seyschab H, Friedl R, Sperling K. Irreversible repression of DNA synthesis in Fanconi anemia cells is alleviated by the product of a novel cyclin-related gene. Mol Cell Biol. 1995 Jan;15(1):305-14.

FOR RESEARCH USE ONLY

December 13, 2016