

ABTS[®] Peroxidase Substrate (1 Component)



Catalog No.	Size
50-66-00	6 x 100 mL
50-66-06	1000 mL
50-66-09	19500 mL
50-66-18	100 mL

DESCRIPTION

ABTS 1-Component Microwell Peroxidase Substrate develops a blue-green product when reacted with horseradish peroxidase labeled conjugates in microwell plates or tubes. The expected appearance of the solution is colorless to light green. Acceptable background absorbance of unreacted substrate is ≤ 0.025 , as measured at 405 nm. ABTS 1-Component Microwell Peroxidase Substrate is not suitable for membrane or immunohistochemical staining. (See KPL's catalog for appropriate substrates.)

FORM/STORAGE/STABILITY

Content:

- 50-66-00 contains 6 x 100 mL ABTS 1-Component Microwell Peroxidase Substrate
- 50-66-06 contains 1 x 1000 mL ABTS 1-Component Microwell Peroxidase Substrate
- 50-66-09 contains 1 x 19500 mL ABTS 1-Component Microwell Peroxidase Substrate
- 50-66-18 contains 1 x 100 mL ABTS 1-Component Microwell Peroxidase Substrate

Store at 2 - 8°C. Stable for a minimum of 1 year when stored at 2 - 8°C.

CONTENT

ABTS 1-Component contains 2,2'-azino-di (3-ethyl-benzthiazoline-6-sulfonate) at a concentration of 0.3 g/L in a glycine/citric acid buffer. The H_2O_2 concentration is 0.01%.

USE

Warm to room temperature before use. Solution is ready to use.

Substrate Development: Following incubation with peroxidase labeled conjugate, wash plate thoroughly. Add 100 μ L substrate solution to each well. As the color develops, tap gently to mix. Incubation times will vary depending on your assay.

To Stop Reaction: Stop reaction by adding an equal volume of ABTS Peroxidase Stop Solution (See RELATED PRODUCTS) or 1% Sodium Dodecyl Sulfate (SDS) to the microwell plate. This will halt color development. ABTS substrate will remain blue-green after addition of stop solution.

To Read Reaction: After stopping, read at a wavelength between 405 - 410 nm. Stopped reaction should be read within 30 minutes.

When to Stop Substrate Reaction: The point at which the substrate reaction is stopped is often determined by the ELISA reader. The O.D. values of the plate should be monitored and the reaction stopped before positive wells are no longer recordable.

To Reduce Substrate Intensity: Background is a sign of over-reaction with ABTS. To reduce the intensity of the substrate reaction, further dilution of the primary antibody and/or conjugate is recommended. Dilution of the substrate is not recommended.

ABSORBANCE MEASUREMENTS

Kinetic Assays:

ABTS substrate produces a blue-green color upon reaction with peroxidase. Read at a wavelength between 405 - 410 nm.

Endpoint Assays:

The addition of 100 μ L (or an equal volume) of stop solution to the microwell plate will halt color development. Read at a wavelength between 405 - 410 nm. Stopped reactions should be read within 30 minutes.

RELATED PRODUCTS

ABTS/HRP Stop Solution	Catalog No. 50-85-01
Wash Solution Concentrate	Catalog No. 50-63-00
BSA Diluent/Blocking Solution Concentrate	Catalog No. 50-61-00
Coating Solution Concentrate	Catalog No. 50-84-00

See KPL's catalog for a list of antibodies, conjugates, substrates and complete systems for microwell ELISA, membrane blotting and immunohistochemical applications.

PRODUCT SAFETY AND HANDLING

See MSDS (Material Safety Data Sheet) for this product.

The product listed herein is for research use only and is not intended for use in human or clinical diagnosis. Nothing disclosed herein is to be construed as a recommendation to use this product in violation of any patents. The information presented above is believed to be accurate. However, said information and product are offered without warranty or guarantee since the ultimate conditions of use and the variability of the materials treated are beyond our control. We cannot be responsible for patent infringements or other violations that may occur with the use of this product. No claims beyond replacement of unacceptable material or refund of purchase price shall be allowed. All claims regarding product performance must be made within 30 days following date of delivery.

Limited Use License

The purchase of this product conveys to the buyer the non-transferable right to use the product in research conducted by the buyer. The buyer cannot sell or otherwise transfer this product or materials made by use of this product to a third party or otherwise use this product or materials made with this product for Commercial Purposes without written approval of KPL, Inc. For additional information, please visit www.kpl.com or the KPL catalog. To obtain a license or approval to use this product for purposes other than those permitted above, contact Director of Sales at (301) 948-7755.