



Ly-6G Antibody [RB6-8C5] (PE)

CATALOG NUMBER: 77-130

Specifications

SPECIES REACTIVITY:	Mouse
TESTED APPLICATIONS:	FACS
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	The RB6-8C5 monoclonal antibody reacts with the mouse Ly-6G (also known as Gr-1).
HOST SPECIES:	Rat

Properties

PURIFICATION:	The monoclonal antibody was purified utilizing affinity chromatography and unreacted dye was removed from the product.
PHYSICAL STATE:	liquid
BUFFER:	Phosphate-buffered aqueous solution, ≤0.09% Sodium azide, may contain carrier protein/stabilizer, pH7.2.
CONCENTRATION:	0.2 mg/mL
STORAGE CONDITIONS:	The product should be stored undiluted at 4°C and should be protected from prolonged exposure to light. Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	Rat IgG2b, kappa
CONJUGATE:	PE

Additional Info

ALTERNATE NAMES:	Gr1, Gr-1, Ly-6G, Ly6g
OFFICIAL SYMBOL:	Ly6g
GENE ID:	546644

Background

BACKGROUND:	The RB6-8C5 monoclonal antibody reacts with the mouse Ly-6G (also known as Gr-1). The Ly-6G protein is a myeloid differentiation antigen of 21-25 kDa, expressed in a regulated manner by the myeloid lineage in the bone marrow, where the level of antigen expression is correlated with the granulocyte maturation and differentiation. In the bone marrow, the antigen is not expressed by the erythroid cells. From the peripheric cells, RB6-8C5 binds with monocytes, neutrophils and eosinophils. As a marker for the mouse monocytes, macrophages and granulocytes, the RB6-8C5 antibody is usually combined with M1/70, a macrophage labeling antibody (Anti-CD11b), for phenotypic analysis.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016