Untitled Page Page 1 of 1



Dextrose, Anhydrous USP

Product No. 1919 Specifications current as of: Jun 8

2011

TEST	SPECIFICATION
GMP Manufactured Product	
Meets U.S.P. Requirements	
Identification	Passes Test
Specific Rotation [a] ²⁵ D (calculated on dried basis)	52.6 - 53.2 °
Color of Solution	Passes Test
Acidity	Passes Test
Water (H ₂ O)	max. 0.5 %
Residue on Ignition	max. 0.1 %
Chloride (CI)	max. 0.018 %
Sulfate (SO ₄)	max. 0.025 %
Arsenic (As)	max. 1 ppm
Heavy Metals (as Pb)	max. 5 ppm
Dextrin	Passes Test
Soluble Starch, Sulfites	Passes Test

No Class 1,2,3 or other solvents are used or produced in the manufacturing or purification of the product.

Bulk Pharmaceutical Chemical

CAUTION: For manufacturing, processing or repacking.

For a Certificate of Lot Analysis, visit www.avantormaterials.com.