



DDR2 Recombinant Protein

CATALOG NUMBER: 92-640

Specifications

SPECIES:	Mouse
SOURCE SPECIES:	Human Cells
SEQUENCE:	Gln24-Arg399
FUSION TAG:	C-6 His tag
APPLICATIONS:	This recombinant protein can be used for biological assays. For research use only.

Properties

PURITY:	Greater than 95% as determined by reducing SDS-PAGE. Endotoxin level less than 0.1 ng/ug (1 IEU/ug) as determined by LAL test.
PREDICTED MOLECULAR WEIGHT:	43.5 kD
PHYSICAL STATE:	Lyophilized
BUFFER:	Lyophilized from a 0.2 um filtered solution of PBS, pH7.4. It is not recommended to reconstitute to a concentration less than 100 ug/ml. Dissolve the lyophilized protein in ddH ₂ O.
STORAGE CONDITIONS:	Lyophilized protein should be stored at -20°C, though stable at room temperature for 3 weeks. Reconstituted protein solution can be stored at 4-7°C for 2-7 days. Aliquots of reconstituted samples are stable at -20°C for 3 months.

Additional Info

ALTERNATE NAMES:	Discoidin domain-containing receptor 2, Discoidin domain receptor 2, CD167 antigen-like family member B, Neurotrophic tyrosine kinase, receptor-related 3, Receptor protein-tyrosine kinase TKT, Tyrosine-protein kinase TYRO10, CD167b, Ddr2, TKT
ACCESSION NO.:	Q62371

Background

Discoidin domain receptor-2 (DDR2) is a cell surface tyrosine kinase receptor that can be activated by soluble collagen and has been implicated in diverse physiological functions including organism growth and wound repair. DDR2 binds to and is activated by collagen I, II, III, V, and X, with the notable exception of basement membrane collagen IV. DDR2 is expressed in connective tissues arising from embryonic mesoderm. DDR2 regulates cell proliferation, cell adhesion, migration, and extracellular matrix remodeling.

FOR RESEARCH USE ONLY

December 14, 2016