



Fc gamma RI Recombinant Protein

CATALOG NUMBER: 92-647

Specifications

SPECIES:	Mouse
SOURCE SPECIES:	Human Cells
SEQUENCE:	Glu25-Pro297
FUSION TAG:	C-6 His tag
APPLICATIONS:	This recombinant protein can be used for biological assays. For research use only.

Properties

PURITY:	Greater than 95% as determined by reducing SDS-PAGE. Endotoxin level less than 0.1 ng/ug (1 IEU/ug) as determined by LAL test.
PREDICTED MOLECULAR WEIGHT:	31.5 kD
PHYSICAL STATE:	Lyophilized
BUFFER:	Lyophilized from a 0.2 um filtered solution of PBS, pH7.4. It is not recommended to reconstitute to a concentration less than 100 ug/ml. Dissolve the lyophilized protein in ddH ₂ O.
STORAGE CONDITIONS:	Lyophilized protein should be stored at -20°C, though stable at room temperature for 3 weeks. Reconstituted protein solution can be stored at 4-7°C for 2-7 days. Aliquots of reconstituted samples are stable at -20°C for 3 months.

Additional Info

ALTERNATE NAMES:	High affinity immunoglobulin gamma Fc receptor I, IgG Fc receptor I, Fc-gamma RI, FcRI, CD64, FCGR1A
ACCESSION NO.:	P26151

Background

CD64, also known as Fc-gamma receptor 1 (Fc gamma RI), is a type of integral membrane glycoprotein that binds monomeric IgG-type antibodies with high affinity. After binding IgG, CD64 interacts with an accessory chain known as the common gamma chain (gamma chain), which possesses an ITAM motif that is necessary for triggering cellular activation. CD64 is composed of a signal peptide, three extracellular immunoglobulin domains of the C2-type used to bind antibody, a hydrophobic transmembrane domain, and a short cytoplasmic tail. CD64 mediates endocytosis, phagocytosis, antibody-dependent cellular cytotoxicity, cytokine release, and superoxide production. It is normally expressed on the surfaces of monocytes and macrophages.

FOR RESEARCH USE ONLY

December 14, 2016