

Material Safety Data Sheet

SPDP

1. Product and company identification

Product name : SPDP

Synonym : 2,5-Pyrrolidinedione, 1-[1-oxo-3-(2-pyridinyldithio)propoxy]-

Chemical formula : C12H12N2O4S2

Supplier: Thermo Fisher Scientific

Pierce Biotechnology

P.O. Box 117 Rockford, IL 61105 United States 815.968.0747 or 800.874.3723 Manufacturer

: Thermo Fisher Scientific Pierce Biotechnology P.O. Box 117 Rockford, IL 61105 United States 815.968.0747 or 800.874.3723

Code : 0021857 0021857B 1876380

 MSDS #
 : 0196

 Validation date
 : 12/17/2010.

 Print date
 : 12/20/2010.

Responsible name : MSDS (Regulatory Specialist)

In case of emergency : CHEMTREC:

800.424.9300 OUTSIDE US: 202.483.7616 Material uses

 Refer to the instruction booklet for proper and intended use. Otherwise, contact supplier for specific

applications.

Product type : Solid.

2. Hazards identification

Emergency overview

Physical state : Solid. [Solid powder.]

Color : White to slightly yellow powder.

Signal word : CAUTION!

Hazard statements : MAY CAUSE EYE AND SKIN IRRITATION. CAN CAUSE TARGET ORGAN DAMAGE.

Precautionary measures : Do not eat, drink or smoke when using this product. Avoid contact with eyes, skin and clothing. Wash thoroughly after handling.

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard

(29 CFR 1910.1200).

Routes of entry : Dermal contact. Eye contact. Inhalation. Ingestion.

Potential acute health effects

Inhalation: Exposure to decomposition products may cause a health hazard. Serious effects may

be delayed following exposure.

Ingestion: No known significant effects or critical hazards.

Skin : Moderately irritating to the skin.

Eyes : Moderately irritating to eyes.

Potential chronic health effects

Chronic effects: Can cause target organ damage.

12/20/2010.

SPDP

2. Hazards identification

Carcinogenicity : No known significant effects or critical hazards. Mutagenicity No known significant effects or critical hazards. No known significant effects or critical hazards. **Teratogenicity**

Developmental effects : No known significant effects or critical hazards. **Fertility effects** No known significant effects or critical hazards.

Target organs : Causes damage to the following organs: upper respiratory tract, skin, eyes.

Over-exposure signs/symptoms

Inhalation : No specific data. Ingestion : No specific data.

Skin : Adverse symptoms may include the following:

> irritation redness

Eyes : Adverse symptoms may include the following:

> irritation watering redness

Medical conditions aggravated by overexposure

Pre-existing disorders involving any target organs mentioned in this MSDS as being at risk may be aggravated by over-exposure to this product.

See toxicological information (Section 11)

3. Composition/information on ingredients

United States

Name	CAS number	%
1-[1-oxo-3-(2-pyridyldithio)propoxy]pyrrolidine-2,5-dione	68181-17-9	98 - 100

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

Eye contact Check for and remove any contact lenses. Immediately flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical

attention immediately.

: In case of contact, immediately flush skin with plenty of water for at least 15 minutes Skin contact

while removing contaminated clothing and shoes. Wash clothing before reuse. Clean

shoes thoroughly before reuse. Get medical attention immediately.

Inhalation Move exposed person to fresh air. If not breathing, if breathing is irregular or if

respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. Loosen tight clothing such as a collar, tie, belt or waistband. Get medical attention

immediately.

Ingestion : Wash out mouth with water. Do not induce vomiting unless directed to do so by medical

personnel. Never give anything by mouth to an unconscious person. Get medical

attention immediately.

Protection of first-aiders No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

Notes to physician : In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.

12/20/2010. 2/8

5. Fire-fighting measures

Flammability of the product : No specific fire or explosion hazard.

Extinguishing media

Suitable

: Use an extinguishing agent suitable for the surrounding fire.

Not suitable

: None known.

Special exposure hazards

: Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable

Hazardous thermal decomposition products : Decomposition products may include the following materials:

carbon dioxide carbon monoxide nitrogen oxides sulfur oxides

Special protective equipment for fire-fighters Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. Accidental release measures

Personal precautions

: No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment (see Section 8).

Environmental precautions

Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods for cleaning up

Small spill

Move containers from spill area. Vacuum or sweep up material and place in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.

Large spill

: Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see section 1 for emergency contact information and section 13 for waste disposal.

7. Handling and storage

Handling

: Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. Do not ingest. Avoid contact with eyes, skin and clothing. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

Storage

Do not store above the following temperature: -20°C (-4°F). Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

8. Exposure controls/personal protection

Canada

Occupational exposure limits

No exposure limit value known.

Consult local authorities for acceptable exposure limits.

Recommended monitoring procedures

: If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment.

Engineering measures

: No special ventilation requirements. Good general ventilation should be sufficient to control worker exposure to airborne contaminants. If this product contains ingredients with exposure limits, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure below any recommended or statutory limits.

Hygiene measures

Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Personal protection

Respiratory

: Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Hands

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Eyes

Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists or dusts.

Skin

Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Environmental exposure

controls

: Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

9. Physical and chemical properties

Physical state : Solid. [Solid powder.]

Color : White to slightly yellow powder.

Molecular weight : 312.37 g/mole Molecular formula : C12H12N2O4S2 **Melting/freezing point** : 85°C (185°F)

10. Stability and reactivity

Chemical stability

: The product is stable.

Conditions to avoid

No specific data.

Incompatible materials Hazardous decomposition : No specific data.

products

: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Possibility of hazardous

: Under normal conditions of storage and use, hazardous reactions will not occur.

reactions

12/20/2010. 4/8

> Life Science Research PO Box 117 Pierce Biotechnology Inc. 3747 N. Meridian Road

Rockford, IL (815) 968-0747 www.thermo.com (815) 968-7316 Fax 61105

11. Toxicological information

United States

Acute toxicity

Conclusion/Summary: To the best of our knowledge, the toxicological properties of this product have not been

thoroughly investigated.

Chronic toxicity

Conclusion/Summary: Not available.

Irritation/Corrosion

Conclusion/Summary: Not available.

<u>Sensitizer</u>

Conclusion/Summary: Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary: Not available.

Teratogenicity

Conclusion/Summary: Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

Canada

Acute toxicity

Conclusion/Summary: To the best of our knowledge, the toxicological properties of this product have not been

thoroughly investigated.

Chronic toxicity

Conclusion/Summary: Not available.

Irritation/Corrosion

Conclusion/Summary: Not available.

Sensitizer

Conclusion/Summary: Not available.

Carcinogenicity

Conclusion/Summary: Not available.

Mutagenicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary: Not available.

Reproductive toxicity

Conclusion/Summary: Not available.

12. Ecological information

Ecotoxicity : No known significant effects or critical hazards.

United States

Aquatic ecotoxicity

Conclusion/Summary: Not available.

Persistence/degradability

Conclusion/Summary: Not available.

Canada

Aquatic ecotoxicity

12/20/2010. 5/8

Life Science Research PO Box 117
Pierce Biotechnology Inc. 9747 N. Meridian Road

Rockford, IL (815) 968-0747 www.thermo.com 61105 (815) 968-7316 Fax

SPDP

12. Ecological information

Conclusion/Summary : Not available.

Persistence/degradability

Conclusion/Summary: Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Waste disposal

: The generation of waste should be avoided or minimized wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Refer to Section 7: HANDLING AND STORAGE and Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION for additional handling information and protection of employees.

14. Transport information

Regulatory information	UN number	Proper shipping name	Classes	PG*
DOT Classification	Not regulated.	-	-	-
IATA-DGR Class	Not regulated.	-	-	-

PG*: Packing group

15. Regulatory information

United States

HCS Classification : Irritating material

Target organ effects

U.S. Federal regulations : TSCA 8(a) IUR Exempt/Partial exemption: Not determined United States inventory (TSCA 8b): Not determined.

SARA 302/304/311/312 extremely hazardous substances: No products were found. SARA 302/304 emergency planning and notification: No products were found.

SARA 302/304/311/312 hazardous chemicals: No products were found.

SARA 311/312 MSDS distribution - chemical inventory - hazard identification: No

products were found.

Clean Air Act Section 112(b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602

: Not listed

Class I Substances

Clean Air Act Section 602 : Not listed

Class II Substances

12/20/2010.

Life Science Research
Pierce Biotechnology Inc.
PO Box 117
3747 N. Meridian Road

Rockford, IL (815) 968-0747 www.thermo.com 61105 (815) 968-7316 Fax

15. Regulatory information

DEA List I Chemicals

: Not listed

(Precursor Chemicals)

DEA List II Chemicals (Essential Chemicals)

: Not listed

State regulations

Massachusetts: This material is not listed.New York: This material is not listed.New Jersey: This material is not listed.Pennsylvania: This material is not listed.

United States inventory

(TSCA 8b)

: Not determined.

Canada

WHMIS (Canada) : Not controlled under WHMIS (Canada).

Canadian lists

Canadian NPRI : This material is not listed.

CEPA Toxic substances : This material is not listed.

Canada inventory : Not determined.

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations.

International regulations

International lists : Australia inventory (AICS): Not determined.

China inventory (IECSC): Not determined.

Japan inventory: Not determined. **Korea inventory**: Not determined.

New Zealand Inventory of Chemicals (NZIoC): This material is listed or exempted.


Philippines inventory (PICCS): Not determined.

16. Other information

Label requirements

: MAY CAUSE EYE AND SKIN IRRITATION. CAN CAUSE TARGET ORGAN DAMAGE.

Hazardous Material Information System (U.S.A.)



The customer is responsible for determining the PPE code for this material.

National Fire Protection Association (U.S.A.)

Health 1 0 Flammability
Instability/Reactivity
Special

Date of printing : **12/20/2010. Date of issue** : 12/17/2010.

Date of previous issue : No previous validation.

Version : 1

12/20/2010. 7/8

61105

Rockford, IL (815) 968-0747

(815) 968-7316 Fax

www.thermo.com

SPDP

16. Other information

Prepared by : MSDS (Regulatory Specialist)

Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.