



Anti-ALKALINE PHOSPHATASE (E.coli) (RABBIT) Antibody - 100-4134

Code: 100-4134

Size: 2 mL

Product Description: Anti-ALKALINE PHOSPHATASE (E.coli) (RABBIT) Antibody - 100-4134

Concentration: 75 mg/mL by Refractometry

PhysicalState: Lyophilized

Label	Unconjugated
Host	Rabbit
Gene Name	phoA
Species Reactivity	E.coli
Buffer	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2
Reconstitution Volume	2.0 mL
Reconstitution Buffer	Restore with deionized water (or equivalent)
Stabilizer	None
Preservative	0.01% (w/v) Sodium Azide
Storage Condition	Store vial at 4° C prior to restoration. For extended storage aliquot contents and freeze at -20° C or below. Avoid cycles of freezing and thawing. Centrifuge product if not completely clear after standing at room temperature. This product is stable for several weeks at 4° C as an undiluted liquid. Dilute only prior to immediate use.
Synonyms	Akp2 antibody, ALP antibody, Nagao isozyme antibody, Placental alkaline phosphatase antibody, Placental like alkaline phosphatase antibody, PLAP 1 antibody, PLAP like antibody, Regan isozyme antibody, Kasahara isozyme antibody
Application Note	Anti-Alkaline Phosphatase (E. Coli) Antibody has been assayed against 1.0 ug of Alkaline Phosphatase [E.coli] in a standard ELISA using Peroxidase conjugated Affinity Purified anti-Rabbit IgG [H&L] (Goat) code #611-1302 and (ABTS (2,2'-azino-bis-[3-ethylbenthiazoline-6-sulfonic acid]) code # ABTS-100 as a substrate for 30 minutes at room temperature. A working dilution of 1:20,000 to 1:100,000 of the reconstitution concentration is suggested for Anti-Alkaline Phosphatase (E. Coli) Antibody.
Background	<p>Alkaline Phosphatase is an enzyme that is key in the hydrolysis of many different types of molecules, resulting in the removal of phosphate groups from said molecule. Most active in basic environments and a common serum analyte, alkaline phosphatase and its isoenzymes are good indicators of bone, liver, and testicular diseases/cancers in immunoassays and diagnostics.</p> <p>Anti-Alkaline Phosphatase (E. Coli) Antibody is ideal for investigators in Cancer, Immunology, and Molecular Biology.</p>
Purity And Specificity	Anti-Alkaline Phosphatase (E. Coli) Antibody was prepared from monospecific antiserum by a delipidation and defibrination. Assay by immunoelectrophoresis resulted in a single precipitin arc against purified and partially purified Alkaline Phosphatase [E.coli]. No cross reactivity occurs against the mammalian form of Alkaline Phosphatase.
Assay Dilutions	User Optimized
ELISA	1:8,000 to 1:40,000
WESTERN BLOT	1:500 - 1:2,000
OTHER ASSAYS	User Optimized
Expiration	Expiration date is one (1) year from date of opening.
Immunogen	Alkaline Phosphatase [E.coli]
General Reference	Moss, D. "Alkaline Phosphatase Isoenzymes." Clin Chem. (1982): Oct. 28 (10): 2007-16.
Related Products	
100-1135	Anti-ALKALINE PHOSPHATASE (Calf Intestine) (GOAT) Antibody - 100-1135

111-1102	Anti-RABBIT IgG (H&L) (GOAT) Antibody - 111-1102
611-1302	Anti-RABBIT IgG (H&L) (GOAT) Antibody Peroxidase Conjugated - 611-1302
B501-0500	BLOTTO Immunoanalytical Grade (Non-Fat Dry Milk) - B501-0500

Related Links

UniProtKB - P00634	http://www.uniprot.org/uniprot/P00634
NCBI - P00634.1	http://www.ncbi.nlm.nih.gov/protein/P00634.1
UniProt - P00634	http://www.uniprot.org/uniprot/P00634
GeneID - 945041	http://www.ncbi.nlm.nih.gov/gene/945041

Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.