



Item Number CE112

Item Microcrystalline Cellulose, Partially

CAS Number 9004-34-6

Molecular Formula

Molecular Weight

Degree of Polymerization.....Max. 350

pH of Solution..... 5.0-7.5

Bulk Density..... To pass test

MAXIMUM LIMITS

Conductivity..... 75 μ S/cm

Loss on Drying..... 7.0%

Residue on Ignition..... 0.1%

Water-Soluble Substances.....0.25%

Ether-Soluble Substances.....0.05%

Heavy Metals.....0.001%

Residual Solvents.....To pass test

Microbial Limits:

..... Total Aerobic Microbial Count

..... 1,000 cfu

..... Total Combined Molds and Yeasts Count

..... 100 cfu

.....Staphylococcus Aureus

..... To pass test

.....Pseudomonas Aeruginosa

..... To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters: East Coast Facility:

14422 S. San Pedro St. 755 Jersey Ave.

Gardena, CA 90248 New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843