



Item Number MA130

Item Magnesium Stearate, NF, BP, JP

CAS Number 557-04-0

Molecular Formula

Molecular Weight

Assay (as Mg; Dried Basis)..... 4.0-5.0%

Relative Content of Stearic Acid and Palmitic Acid..... To pass test

MAXIMUM LIMITS

Microbial Limits:

|Total Aerobic Microbial Count..... 1000 cfu/g

|Total Combined Molds and Yeasts Count.....500 cfu/g

|Tests for Salmonella Species and Escherichia coli..... Negative

Acidity or Alkalinity..... To pass test

Loss on Drying..... 6.0%

Lead..... 10 ppm

Chloride..... 0.1%

Sulfate.....0.5%

Heavy Metals.....20 ppm

Cadmium..... 3 ppm

Nickel..... 5 ppm

Residual Solvents.....To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters: East Coast Facility:

14422 S. San Pedro St. 755 Jersey Ave.

Gardena, CA 90248 New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843