



Item Number R1005
Item Resorcinol, Crystalline Powder, USP
CAS Number 108-46-3
Molecular Formula $C_6H_6O_2$
Molecular Weight 110.11

Assay (Dried Basis)..... 99.0-100.5%
Melting Range..... 109°-111°C

MAXIMUM LIMITS

Loss on Drying..... 1.0%
Residue on Ignition..... 0.05%
Phenol..... To pass test
Catechol..... To pass test
Ordinary Impurities..... 1.0%
Residual solvents..... To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters: East Coast Facility:

14422 S. San Pedro St. 755 Jersey Ave.

Gardena, CA 90248 New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843