

Anti-HUMAN CRP (GOAT) Antibody - 109-1132

Code: 109-1132

Size: 2 mL

Product Description: Anti-HUMAN CRP (GOAT) Antibody - 109-1132

Concentration: 90 mg/mL by Refractometry

PhysicalState: Lyophilized

Label	Unconjugated
Host	Goat
Gene Name	CRP
Species Reactivity	human
Buffer	0.01 M Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2
Reconstitution Volume	2.0 mL
Reconstitution Buffer	Restore with deionized water (or equivalent)
Stabilizer	None
Preservative	None
Storage Condition	Store vial at 4° C prior to restoration. For extended storage aliquot contents and freeze at -20° C or below. Avoid cycles of freezing and thawing. Centrifuge product if not completely clear after standing at room temperature. This product is stable for several weeks at 4° C as an undiluted liquid. Dilute only prior to immediate use.
Synonyms	C reactive protein pentraxin related antibody, CRP antibody, MGC88244 antibody, PTX 1 antibody, PTX1 antibody
Purity And Specificity	This product was prepared from monospecific antiserum by a delipidation and defibrination. Assay by immunoelectrophoresis resulted in a single precipitin arc against purified and partially purified Capsular Reactive Protein (CRP) [Human Serum]. Cross reactivity against Capsular Reactive Protein (CRP) from other tissues and species may occur but have not been specifically determined.
Assay Dilutions	User Optimized
ELISA	1:20,000 - 1:100,000
Immunohistochemistry	1:1,000 - 1:5,000
WESTERN BLOT	1:2,000 - 1:10,000
IHC	1:1,000 - 1:5,000
OTHER ASSAYS	User Optimized
Expiration	Expiration date is one (1) year from date of opening.
Immunogen	Capsular Reactive Protein (CRP) [Human Serum]

Related Products

009-001-310	IL-6 Human Recombinant Protein - 009-001-310
205-3202	Anti-GOAT IgG (H&L) (MOUSE) Antibody Fluorescein Conjugated - 205-3202
205-4307	Anti-GOAT IgM (mu) (RABBIT) Antibody Peroxidase Conjugated - 205-4307

Related Links

UniProtKB	http://www.uniprot.org/uniprot/P02741
NCBI - NP_000558.2	http://www.ncbi.nlm.nih.gov/protein/NP_000558.2

UniProt - P02741 <http://www.uniprot.org/uniprot/P02741>

Gene ID - 1401 <http://www.ncbi.nlm.nih.gov/gene/1401>

Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.