


PRAMEF20 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12142b	WB, E	H	NP_001093584.1 , Q5VT98 , NP_001093322.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31008

Application Data: **Calculated MW: 54770 Da**



PRAMEF20 Antibody (C-term) (Cat. #AP12142b) western blot analysis in MDA-MB435 cell line lysates (35ug/lane). This demonstrates the PRAMEF20 antibody detected the PRAMEF20 protein (arrow).

Gene ID: [645425](#), [391001](#) **Gene Symbol:** PRAMEF20

Other Names:

PRAMEF20, PRAME family member 20/21,

Target/Specificity:

This PRAMEF20 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 401-431 amino acids from the C-terminal region of human PRAMEF20.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

PRAMEF20 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
