


KCNJ4 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12298a	WB, E	H	P48050 , NP_690607.1 , NP_004972.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31068

Application Data:

Calculated MW: 49500 Da



KCNJ4 Antibody (N-term) (Cat. #AP12298a) western blot analysis in CEM cell line lysates (35ug/lane). This demonstrates the KCNJ4 antibody detected the KCNJ4 protein (arrow).

Gene ID:	Gene Symbol:
3761	KCNJ4

Other Names:

KCNJ4;Inward rectifier potassium channel 4;IRK3

Target/Specificity:

This KCNJ4 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1-30 amino acids from the N-terminal region of human KCNJ4.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

KCNJ4 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

KCNJ4 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
