ZNF845 Antibody (N-term)


Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12359a	WB, E	H	NP_612383.1, Q96IR2

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31207

Application Data:

Calculated MW: 113133 Da



ZNF845 Antibody (N-term) (Cat. #AP12359a) western blot analysis in ZR-75-1 cell line lysates (35ug/lane).This demonstrates the ZNF845 antibody detected the ZNF845 protein (arrow).

Gene ID:	Gene Symbol:
91664	ZNF845

Other Names:

ZNF845;Zinc finger protein 845;

Target/Specificity:

This ZNF845 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 79-108 amino acids from the N-terminal region of human ZNF845.

Application Notes:

The suggested dilution is:
ELISA 1:1,000
Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

ZNF845 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

ZNF845 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.