

Anti-DOG IgG F(c) (RABBIT) Antibody Alkaline Phosphatase Conjugated - 604-4503

Code: 604-4503

Size: 1 mg

Product Description: Anti-DOG IgG F(c) (RABBIT) Antibody Alkaline Phosphatase Conjugated - 604-4503

Concentration: 1.0 mg/mL by UV absorbance at 280 nm

PhysicalState: Liquid (sterile filtered)

Label	Alkaline Phosphatase (Calf Intestine)
Host	Rabbit
Buffer	0.05 M Tris Chloride, 0.15M Sodium Chloride, 0.001M Magnesium Chloride, 0.0001M Zinc Chloride, 50% (v/v) Glycerol; pH 8.0
Stabilizer	10 mg/mL Bovine Serum Albumin (BSA) - Immunoglobulin and Protease free
Preservative	0.1% (w/v) Sodium Azide
Storage Condition	Store vial at 4° C before opening. DO NOT FREEZE. This product is stable at 4° C as an undiluted liquid. Dilute only prior to immediate use. Freezing alkaline phosphatase conjugates will result in a substantial loss of enzymatic activity.
Synonyms	ALP, Alk Phos
Application Note	This product has been assayed against 1.0 ug of Dog IgG in a standard capture ELISA using pNPP p-nitrophenyl phosphate code # NPP-10 as a substrate for 30 minutes at room temperature. A working dilution of 1:3,000 to 1:44,000 of the reconstitution concentration is suggested for this product.
Purity And Specificity	This product was prepared from monospecific antiserum by immunoaffinity chromatography using Dog IgG coupled to agarose beads followed by solid phase adsorption(s) to remove any unwanted reactivities. Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Alkaline Phosphatase (calf intestine), anti-Rabbit Serum, Dog IgG, Dog IgG F(c) and Dog Serum. No reaction was observed against Dog IgG F(ab).
Assay Dilutions	User Optimized
ELISA	1:2,000 - 1:10,000
Immunohistochemistry	1:200 - 1:1,000
WESTERN BLOT	1:500 - 1:2,500
IHC	1:200 - 1:1,000
OTHER ASSAYS	User Optimized
Expiration	Expiration date is one (1) year from date of opening.
Immunogen	Dog IgG F(c) fragment
Related Products	<div>610-4302 Anti-MOUSE IgG (H&L) (RABBIT) Antibody Peroxidase Conjugated - 610-4302</div> <div>611-1302 Anti-RABBIT IgG (H&L) (GOAT) Antibody Peroxidase Conjugated - 611-1302</div> <div>B304 NORMAL GOAT SERUM (NGS) - B304</div> <div>BSA-50 BOVINE SERUM ALBUMIN - Fraction V (Immunoglobulin and Protease Free) - BSA-50</div>

Related Links

Images

1	Dot Blot of Rabbit anti-Dog IgG Fc Antibody Alkaline Phosphatase Conjugated. Antigen: Dog IgG. Load: Lane 1 - 200 ng Lane 2 - 66.7 ng Lane 3 - 22.2 ng Lane 4 - 7.41 ng Lane 5 - 2.47 ng. Primary antibody: n/a. Secondary antibody: Rabbit anti-Dog IgG Fc Antibody Alkaline Phosphatase Conjugated at 1:1,000 for 1 HR
---	--

at RT.Block: MB-070 for 1 HR at RT.



Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.