


GCSH Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16949a	WB, E	H	P23434
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB36545

Application Data:
Calculated MW: 18885 Da


GCSH Antibody (N-term) (Cat. #AP16949a) western blot analysis in T47D cell line lysates (35ug/lane). This demonstrates the GCSH antibody detected the GCSH protein (arrow).

Gene ID:	Gene Symbol:
2653	GCSH

Other Names:

Glycine cleavage system H protein, mitochondrial;GCSH;

Target/Specificity:

This GCSH antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 26-56 amino acids from the N-terminal region of human GCSH.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

GCSH Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

GCSH Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
