


Mouse Axl Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

| | | | |
|-----------------------|----------------------|--------------------|------------------------|
| Catalog # | Applications: | Reactivity: | Accessions: |
| AP16023a | WB, E | H, M(predict) | Q00993 |
| Concentration: | Size: | Isotype: | Clone Name: |
| 0.25 mg/ml | 0.1 mg | Rabbit Ig | RB34738 |

Application Data: **Calculated MW: 98251 Da**



Mouse Axl Antibody (N-term) (Cat. #AP16023a) western blot analysis in K562 cell line lysates (35ug/lane). This demonstrates the Axl antibody detected the Axl protein (arrow).

Gene ID: [26362](#) **Gene Symbol:** Axl

Other Names:

Tyrosine-protein kinase receptor UFO;Axl;Ark; Ufo

Target/Specificity:

This Mouse Axl antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 121-149 amino acids from the N-terminal region of human Mouse Axl.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Mouse Axl Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term

storage, place the at -20°C.

Precautions:

Mouse Axl Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
