


## Mouse Cdk18 Antibody (C-term)

### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP16070b	WB, E	M	<a href="#">NP_032821.1</a> , <a href="#">Q04899</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35466

#### Application Data:

Calculated MW: 51848 Da



Mouse Cdk18 Antibody (C-term) (Cat. #AP16070b) western blot analysis in mouse stomach tissue lysates (35ug/lane). This demonstrates the Cdk18 antibody detected the Cdk18 protein (arrow).

<b>Gene ID:</b>	<b>Gene Symbol:</b>
<a href="#">18557</a>	Cdk18

#### Other Names:

Cell division protein kinase 18;Cdk18;Pctk3

#### Target/Specificity:

This Mouse Cdk18 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 421-449 amino acids from the C-terminal region of Mouse Cdk18.

#### Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

#### Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

#### Storage:

Mouse Cdk18 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term

storage, place the at -20&deg;C.

---

**Precautions:**

Mouse Cdk18 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---