ANKHD1 Antibody (N-term)


Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16216a	WB, E	H	NP_060217.1, NP_078944.2, NP_060448.1, Q8IWZ3, NP_065741.3

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35678

Application Data:

Calculated MW: 65kd Isoform 2. 269458 Da



ANKHD1 Antibody (N-term) (Cat. #AP16216a) western blot analysis in HL-60 cell line lysates (35ug/lane).This demonstrates the ANKHD1 antibody detected the ANKHD1 protein (arrow).

Gene ID:	Gene Symbol:
54882	ANKHD1

Other Names:

Ankyrin repeat and KH domain-containing protein 1;ANKHD1;KIAA1085; MASK; VBARP

Target/Specificity:

This ANKHD1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 444-474 amino acids from the N-terminal region of human ANKHD1.

Application Notes:

The suggested dilution is:
ELISA 1:1,000
Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

ANKHD1 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

ANKHD1 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.