


## Mouse Irak3 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP14260b	WB, E	M	<a href="#">Q8K4B2</a> , <a href="#">NP_082955.2</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34795

**Application Data:** **Calculated MW: 68455 Da**



Mouse Irak3 Antibody (C-term) (Cat. #AP14260b) western blot analysis in mouse kidney tissue lysates (35ug/lane). This demonstrates the Irak3 antibody detected the Irak3 protein (arrow).

**Gene ID:** [73914](#)  
**Gene Symbol:** [Irak3](#)

### Other Names:

Interleukin-1 receptor-associated kinase 3;Irak3;

### Target/Specificity:

This Mouse Irak3 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 516-544 amino acids from the C-terminal region of Mouse Irak3.

### Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

### Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

### Storage:

Mouse Irak3 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term

storage, place the at -20&deg;C.

---

**Precautions:**

Mouse Irak3 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---